

EVOLine® SPECIFICATIONS

INSTALLATION INSTRUCTIONS

- A hole saw of 102mm diameter is required to fit the EVOLine® Port.
- If the EVOLine® Port is fitted into a kitchen benchtop, a “bead” of silicon is recommended to seal the EVOLine® Port.
- When the EVOLine® Port is retracted, a minimum void of 330mm is required from the top of the benchtop or desk surface. Diameter of void is 102mm. A clear diameter of 140mm on the underside of the top is required for the locking flange.
- We recommend for older homes to use the EVOLine® Port with RCD.

POSITIONING OF POWER PORT:

We recommend as a general rule that the EVOLine® Port be positioned at least 500mm horizontally and 1m vertically from any kitchen sink. However, an EVOLine® Port can be located up to 150mm horizontally and 400mm vertically from a sink if the sink has a capacity less than 45 litres. Any power port closer than these dimensions must be of the type that is protected by its residual current device. But, to be safe, stick to 500mm horizontally and 1m vertically away from water.

NB: Product shown in attached installation diagrams is the European model showing European electrical sockets used for demonstration purposes only. EVOLine® Port available in New Zealand and Australia to local standards.

Montageanleitung – Oberschrank
Assembly Instructions – Overhead installation
Instructions de montage – Iliment mural
Pour installation dans élément suspendu



Achtung!

Der Oberschrank muss durch zusätzliche Befestigungsschrauben an der Wand gesichert werden.


Important, please read!

Please ensure that the overhead structure (e.g. shelf, cabinet, etc.) is securely fixed to the wall when performing an overhead installation.

Attention!

En cas de fixation de EVoline® Port sur un élément mural, il est indispensable que cet élément soit sécurisé par une fixation supplémentaire.

Montageanleitung – Arbeitsplatte
Assembly Instructions – Work surface installation
Instructions de montage – Plateau



Lochsäge Ø 102 mm
bestellbar unter Artikel-Nr. 990.90.170

Hole saw Ø 102 mm
order number 990.90.170

Diamètre de perçage Ø 102 mm
pour commander Article Référence: 990.90.170